

Tube: Diagnostic Rotating Anode Tubes – Medical & Veterinary Use

Model Numbers and Specifications

Tube Type	Max Operating Voltage (KV)	Nominal Focal Spot Value	Anode Heat Storage Capacity (KG)	Max Rating (KW) (0.1S)	Filament Max Current (A)	Data Max Voltage (V)	Target Angle (degree)	Anode Rotating Speed (r/min)	Outline Diameter (mm)	Dimension Length (mm)	Remarks
XD51-20, 40/100	100 100	1.0 2.0	100 100	20 40	5.5 5.5	9 13	17.5 17.5	2800 2800	108 108	250 250	
XD51-20, 40/125	125 125	1.0 2.0	100 100	20 40	5.5 5.5	9 13	17.5 17.5	2800 2800	108 108	250 250	
XD51-20, 17/125	125	0.8	212	17	5.5	7	14.0	2800	108	250	Replace RAD74
XD51-6, 20/125	125 125	0.5 1.0	100 100	6 20	5.5 5.5	7 9	17.5 17.5	2800 2800	108 108	250 250	
XD51-10, 40/125	125 125	0.6 1.5	300 300	10 40	5.5 5.5	9 13	14.0 14.0	2800 2800	108 108	250 250	Replace RAD74
XD51-22, 47/125	125 125	1.0 2.0	110 110	22 47	5.5 5.5	9 13	16.0 16.0	2800 2800	108 108	246 246	
XD55-10/100	100	0.8	44	10	4.5	7	17.5	2800	78	212	
XD55-10, 27/100	100 100	0.8 1.8	44 44	10 27	5.5 5.5	9 13	17.5 17.5	2800 2800	78 78	212 212	
XD55-10, 27/125	125 125	0.8 1.8	44 44	10 27	5.5 5.5	9 13	17.5 17.5	2800 2800	78 78	212 212	
XD52-30, 50/125	125 125	1.0 2.0	140 140	30 50	5.5 5.5	9 13	17.5 17.5	2800 2800	120 120	265 265	
XD52-30, 50/150	150 150	1.0 2.0	140 140	30 50	5.5 5.5	9 13	17.5 17.5	2800 2800	120 120	265 265	
XD52-10, 40/125	125 125	0.6 1.6	140 140	10 40	5.5 5.5	8 13	17.5 17.5	2800 2800	120 120	265 265	
XD52-10, 40/150	150 150	0.6 1.6	140 140	10 40	5.5 5.5	8 13	17.5 17.5	2800 2800	120 120	265 265	
XD52-20, 40/125	125 125	0.6 1.2	140 140	20 40	5.5 5.5	9 13	12.0 12.0	2800 2800	120 120	265 265	
XD52-20, 40/150	150 150	0.6 1.2	140 140	20 40	5.5 5.5	9 13	12.0 12.0	2800 2800	120 120	265 265	
XD52-2, 40/125	125 125	0.3 1.6	140 140	2 40	4.5 5.5	4.5 13	17.5 17.5	2800 2800	120 120	265 265	
XD52-2, 40/125	150 150	0.3 1.6	140 150	2 40	4.5 5.5	4.5 13	17.5 17.5	2800 2800	120 120	265 265	
XD60C-0.9, 2.4/39	39 39	0.3 0.6	44 44	0.9 2.4	4.8 5	4 6	17.5 17.5	2800 2800	78 78	212 212	Mo Target
XD60-1.2, 5.5/4.9	49 49	0.3 0.6	100 100	1.2 5.5	4 5	4 5.5	17.5 17.5	2800 2800	108 108	200 200	Mo Target
XH01	150 150	0.6 1.2	120 120	20 46	5.5 5.5	9 15	12.5 12.5	2800 2800	108 108	251 251	Re-W Re-W
XH02	150 150	0.6 1.2	212 212	32 70	5.5 5.5	9 15	12.0 12.0	8400 8400	137 137	255 255	Re-W Re-W
XH03	150 150	0.6 1.2	212 212	32 70	5.5 5.5	9 15	12.0 12.0	8400 8400	120 120	270 270	Re-W Re-W
XD56-3.8, 10/130	130 130	0.3 0.6	80 80	3.8 10	4.5 4.5	3.5 7	16.0 16.0	2800 2800	80 80	219 219	Re-W Re-W
XD56-5, 17/130	130 130	0.3 0.6	210 210	5 17	4.5 4.5	3.5 7	10.0 10.0	2800 2800	80 80	214 214	Re-W Re-W
XD56-11, 32/130	130 130	0.6 1.3	80 80	11 32	4.5 4.5	6.5 8	16.0 16.0	2800 2800	80 80	219 219	Re-W Re-W
X787	49 49	0.3 0.6	44 44	1.2 5.5	4.5 4.5	3 6	12.0 12.0	2800 2800	70 70	217 217	Mo Mo